

## Technical Data Sheet



### ASSEMBLY MATERIALS

**Product Type:** SMT Adhesive

**Product Name:** PD 955 PRM

#### Description

PD 955 PRM is a thermosetting single component, solvent-free polymer adhesive, developed especially for the surface mounting of SMT components onto PCBs and for use on bare substrates. This rheology is specially adapted for printing application with thick stencils. PD 955 PRM is optimized to clean the stencil easily.

#### Key Benefits

- Excellent adhesion with standard and also with difficult to glue components
- Very high green strength prevents component movement during placement
- Ideal, high dot form and excellent consistency of the glue dots

#### Applications

- Printing
- Pin Transfer

#### Physical Properties

Processing time at 20 – 30°C (days)	Curing Profile	Colour
Max. 2	The standard curing conditions are 125°C / 3 minutes. As long as the curing profile is respected, the adhesive can withstand reflow conditions according IPC/JEDEC J-STD-020.	Pink
	<b>Temperature (°C)</b>	
	100   125   150   180	
	<b>Time (min)</b>	
	8   3   1.5   1	

#### Cleaning Instructions

**Before curing:** The adhesive can be removed with Zestron HC and other Zestron and Vigon cleaning materials. Do not use alcohol as this will cure the adhesive. Cleaned dispensing units should be completely dried before installation.

**After Curing:** Defective components can be replaced by heating (with hot air) the cured adhesive joint above 100 °C. After removing the component (torsion movement), the hot air should be focused on the remaining adhesive in order to remove it with a sharp tool.

#### Adhesive Conditioning

- Remove adhesive from fridge: Before opening the package leave it for at least 2 hours at room temperature so that adhesive heats up
- Do not open cartridge while adhesive is cold to prevent condensation

## Technical Data Sheet

### Storage

- Store the SMT-adhesive in originally-sealed containers and avoid exposure to high humidity and sunlight
- Store cartridges with tip pointing downwards
- Max. expiration date: Shelf life: Please refer to the expiry date on the label of the packaged product
- Storage condition in the refrigerator at 2 - 10 °C

**Heraeus Electronics**  
Heraeus Deutschland GmbH & Co. KG  
Heraeusstraße 12 – 14  
63450 Hanau, Germany  
[www.heraeus-electronics.com](http://www.heraeus-electronics.com)

**Japan**  
Phone +81 (3) 6902 6585  
[electronics.japan@heraeus.com](mailto:electronics.japan@heraeus.com)

**Americas**  
Phone +1 610 825 6050  
[electronics.americas@heraeus.com](mailto:electronics.americas@heraeus.com)

**Asia Pacific**  
Phone +65 6571 7649  
[electronics.apac@heraeus.com](mailto:electronics.apac@heraeus.com)

**China**  
Phone +86 21 3357 5457  
[electronics.china@heraeus.com](mailto:electronics.china@heraeus.com)

**Europe, Middle East and Africa**  
Phone +49 6181 35 3627  
[electronics.emea@heraeus.com](mailto:electronics.emea@heraeus.com)